



FBH056

FBH056 1xPL-C/2P10W I WH

1, MASTER PL-C 2 Pin, 10 W, White

The FBH and FBS family of recessed downlights come complete with a highly efficient frosted aluminum reflector and polished strip faceted upper surface. They are specially designed for compact fluorescent 10W/13W/18W/26W lamps. A standard ballast is integrated with the luminaires. A clear glass option is available upon request.

Product data

General Information	
Lamp family code	PL-C/2P [MASTER PL-C 2 Pin]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Optical cover type	-
Operating and Electrical	
Power Consumption	10 W
Mechanical and Housing	
Housing Color	White
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Product Data	
Order product name	FBH056 1xPL-C/2P10W I WH
Full product name	FBH056 1xPL-C/2P10W I WH
Full product code	911401153780
Order code	911401153780
Material Nr. (12NC)	911401153780
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828601140
Numerator - Packs per outer box	1
EAN/UPC - Case	6923828601140

FBH056

Dimensional drawing

