



# FBH057

## FBH057 1xPL-C/2P13W I FG WH

1 pc - MASTER PL-C 2 Pin - 13 W - Inductive - Flat glass - White


The FBH and FBS family of recessed downlights come complete with a highly efficient frosted aluminum reflector and polished strip faceted upper surface. They are specially designed for compact fluorescent 10W/13W/18W/26W lamps. A standard ballast is integrated with the luminaires. A clear glass option is available upon request.

### Product data

General Information	
Number of light sources	1 [ 1 pc]
Lamp family code	PL-C/2P [ MASTER PL-C 2 Pin]
Lamp power	13 W
Compensation circuit	Inductive
Gear	CONV [ Conventional]
Optical cover/lens type	FG [ Flat glass]
Approval and Application	
Ingress protection code	IP20 [ Finger-protected]
Product Data	
Full product code	911401153880



Order product name	FBH057 1xPL-C/2P13W I FG WH
EAN/UPC – product	6923828601188
Order code	911401153880
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	911401153880
Net weight (piece)	0.859 kg

## Dimensional drawing



## FBH/FBS057

### Photometric data



IFGU1\_FBH057 1xPL-C2P13W FG.EPS

IFPC1\_FBH057 1xPL-C2P13W FG.EPS

