



FBH056

FBH056 1xPL-C/2P10W I FG WH

1 pc - MASTER PL-C 2 Pin - 10 W - Inductive - Flat glass - White

The FBH and FBS family of recessed downlights come complete with a highly efficient frosted aluminum reflector and polished strip faceted upper surface. They are specially designed for compact fluorescent 10W/13W/18W/26W lamps. A standard ballast is integrated with the luminaires. A clear glass option is available upon request.

Product data


General Information	
Number of light sources	1 [1 pc]
Lamp family code	PL-C/2P [MASTER PL-C 2 Pin]
Lamp power	10 W
Compensation circuit	Inductive
Gear	CONV [Conventional]
Optical cover/lens type	FG [Flat glass]

Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Product Data	
Full product code	911401154680



Order product name	FBH056 1xPL-C/2P10W I FG WH
EAN/UPC – product	6923828601171
Order code	911401154680
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	911401154680
Net weight (piece)	0.779 kg

Dimensional drawing



FBH/FBS056

Photometric data



IFGU1_FBH056 1xPL-C2P10W FG.EPS

IFPC1_FBH056 1xPL-C2P10W FG.EPS

