



VerseBay Elite MPK518

MPK518 CDM-TMW315W EB WB

MASTERColour CDM-T Elite MW, 315 W, Electronic, Wide beam

Manufacturing customers want energy-efficient lighting solutions to help ensure their factories are green. Versebay Elite is a high-bay luminaire incorporating high-efficacy CDM Elite lamp technology, as well as extremely efficient gear, which almost halves energy consumption compared with a conventional metal-halide solution. It also provides brilliant lighting performance with excellent color rendering. Versebay Elite's choice of wide and narrow beams makes it suitable for a variety of applications. The luminaire's robust construction and high ingress protection also mean it can be deployed in the most demanding, heavy-duty working environments.

Product data

General Information		Power Consumption	
Lamp family code	CDM-TMW [MASTERColour CDM-T Elite MW]	315 W	
Gear	EB [Electronic]	Approval and Application	
Flammability mark	For mounting on normally flammable surfaces	Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Light Technical		Protection class IEC	Safety class I
Number of light sources	1	Product Data	
Optic type	Wide beam	Order product name	MPK518 CDM-TMW315W EB WB
Optical cover type	Prismatic refractor	Full product name	MPK518 CDM-TMW315W EB WB
Operating and Electrical		Full product code	911401504201
Input Voltage	230 to 240 V	Order code	911401504201
Line Frequency	50 Hz	Material Nr. (12NC)	911401504201
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	2

Dimensional drawing

