



VerseBay Elite MPK518

MPK518 CDM-TMW315W EB NB

MASTERColour CDM-T Elite MW, 315 W, Electronic, Narrow beam

Manufacturing customers want energy-efficient lighting solutions to help ensure their factories are green. Versebay Elite is a high-bay luminaire incorporating high-efficacy CDM Elite lamp technology, as well as extremely efficient gear, which almost halves energy consumption compared with a conventional metal-halide solution. It also provides brilliant lighting performance with excellent color rendering. Versebay Elite's choice of wide and narrow beams makes it suitable for a variety of applications. The luminaire's robust construction and high ingress protection also mean it can be deployed in the most demanding, heavy-duty working environments.

Product data

General Information	
Lamp family code	CDM-TMW [MASTERColour CDM-T Elite MW]
Gear	EB [Electronic]
Flammability mark	For mounting on normally flammable surfaces
Light Technical	
Number of light sources	1
Optic type	Narrow beam
Optical cover type	Prismatic refractor
Operating and Electrical	
Input Voltage	230 to 240 V
Line Frequency	50 Hz

Power Consumption	315 W
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Protection class IEC	Safety class I
Product Data	
Order product name	MPK518 CDM-TMW315W EB NB
Full product name	MPK518 CDM-TMW315W EB NB
Full product code	911401504401
Order code	911401504401
Material Nr. (12NC)	911401504401
Numerator - Quantity Per Pack	1

VerseBay Elite MPK518

Numerator - Packs per outer box	2
---------------------------------	---

Dimensional drawing

