



Essential SmartBright Slim Batten

BN068C LED5/CW L600

Essential SmartBright Slim Batten, 7 W, 6500 K

A flexible solution for long linear light for ambient lighting.

Product data

| General Information | |
|------------------------------------|---------------|
| Light source replaceable | No |
| Driver included | Yes |
| CE mark | - |
| Flammability mark | - |
| ENEC mark | - |
| Light Technical | |
| Correlated Color Temperature (Nom) | 6500 K |
| Optic type | - |
| Luminaire light beam spread | 110° |
| Operating and Electrical | |
| Input Voltage | 220-240 V |
| Line Frequency | 50 to 60 Hz |
| Power Consumption | 7 W |
| Power Factor (Fraction) | 0.5 |
| Temperature | |
| Ambient temperature range | -20 to +35 °C |

| Controls and Dimming | |
|-------------------------------------|----------------------------|
| Dimmable | No |
| Driver/power unit/transformer | Power supply unit (On/Off) |
| Mechanical and Housing | |
| Housing Material | Polycarbonate |
| Optic material | Polycarbonate |
| Housing Color | White |
| Approval and Application | |
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK02 [0.2 J standard] |
| Protection class IEC | Safety class I |
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | +/-10% |
| Power consumption tolerance | +/-10% |
| Application Conditions | |
| Maximum dim level | Not applicable |

Essential SmartBright Slim Batten

| Product Data | |
|---------------------|---------------------|
| Order product name | BN068C LED5/CW L600 |
| Full product name | BN068C LED5/CW L600 |
| Full product code | 871016330108299 |
| Order code | 30108299 |
| Material Nr. (12NC) | 911401504431 |

| | |
|---------------------------------|---------------|
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8710163301082 |
| Numerator - Packs per outer box | 24 |
| EAN/UPC - Case | 8710163301204 |

Dimensional drawing

