



# Essential SmartBright Slim Batten

## BN068C LED5/CW L600

Essential SmartBright Slim Batten, 7 W, 6500 K

A flexible solution for long linear light for ambient lighting.

### Product data

| General Information                |               |
|------------------------------------|---------------|
| Light source replaceable           | No            |
| Driver included                    | Yes           |
| CE mark                            | -             |
| Flammability mark                  | -             |
| ENEC mark                          | -             |
| Light Technical                    |               |
| Correlated Color Temperature (Nom) | 6500 K        |
| Optic type                         | -             |
| Luminaire light beam spread        | 110°          |
| Operating and Electrical           |               |
| Input Voltage                      | 220-240 V     |
| Line Frequency                     | 50 to 60 Hz   |
| Power Consumption                  | 7 W           |
| Power Factor (Fraction)            | 0.5           |
| Temperature                        |               |
| Ambient temperature range          | -20 to +35 °C |

| Controls and Dimming                |                            |
|-------------------------------------|----------------------------|
| Dimmable                            | No                         |
| Driver/power unit/transformer       | Power supply unit (On/Off) |
| Mechanical and Housing              |                            |
| Housing Material                    | Polycarbonate              |
| Optic material                      | Polycarbonate              |
| Housing Color                       | White                      |
| Approval and Application            |                            |
| Ingress protection code             | IP20 [Finger-protected]    |
| Mech. impact protection code        | IK02 [0.2 J standard]      |
| Protection class IEC                | Safety class I             |
| Initial Performance (IEC Compliant) |                            |
| Luminous flux tolerance             | +/-10%                     |
| Power consumption tolerance         | +/-10%                     |
| Application Conditions              |                            |
| Maximum dim level                   | Not applicable             |

# Essential SmartBright Slim Batten

| Product Data                    |                     |
|---------------------------------|---------------------|
| Full product code               | 871016330108299     |
| Order product name              | BN068C LED5/CW L600 |
| Order code                      | 911401504431        |
| Numerator - Quantity Per Pack   | 1                   |
| Numerator - Packs per outer box | 24                  |

|                        |                     |
|------------------------|---------------------|
| Material Nr. (12NC)    | 911401504431        |
| Full product name      | BN068C LED5/CW L600 |
| EAN/UPC - Case         | 8710163301204       |
| EAN/UPC - Product/Case | 8710163301082       |

## Dimensional drawing

