



# Essential SmartBright Slim Batten

## BN068C LED9/NW L900

Essential SmartBright Slim Batten, 10 W, 4000 K

A flexible solution for long linear light for ambient lighting.

### Product data

General Information	
Light source replaceable	No
Driver included	Yes
CE mark	-
Flammability mark	-
ENEC mark	-
Light Technical	
Correlated Color Temperature (Nom)	4000 K
Optic type	-
Luminaire light beam spread	110°
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Power Consumption	10 W
Power Factor (Fraction)	0.5
Temperature	
Ambient temperature range	-20 to +35 °C

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Mechanical and Housing	
Housing Material	Polycarbonate
Optic material	Polycarbonate
Housing Color	White
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Application Conditions	
Maximum dim level	Not applicable

# Essential SmartBright Slim Batten

Product Data	
Order product name	BN068C LED9/NW L900
Full product name	BN068C LED9/NW L900
Full product code	871016330104499
Order code	30104499
Material Nr. (12NC)	911401504831

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163301044
Numerator - Packs per outer box	24
EAN/UPC - Case	8710163301167

## Dimensional drawing

