



GreenUp Lowbay G2

BY288P LED90/CW PSU

GreenUp Lowbay G2, 75 W, 8800 lm, 6500 K, 102°

Good lighting is essential in industrial workspaces and large indoor areas. The wrong choice of lights or a lighting not correctly planned can lead to eye strain, fatigue, and poor performance, compromising safety and productivity. The Philips GreenUp Lowbay G2 luminaire is a simple LED solution which efficiently illuminates work areas, creating a brighter and better work, retail or sporting environment. With its crisp, white light and high color rendering index coupled with energy efficiency, high visibility and enhances safety 24/7. Equipped with motion detection function, this easy-to-install and low-maintenance lighting solution is suitable for a variety of applications.

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
Service tag	Yes
CE mark	CE mark
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 5 s
Light Technical	
Luminous Flux	8,800 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	117 lm/W

Color rendering index (CRI)	>80
Light source color	Cool white
Optical cover type	Opal
Luminaire light beam spread	102°
Operating and Electrical	
Input Voltage	220-400 V
Line Frequency	50 or 60 Hz
Inrush current	8.6 A
Inrush time	0.05 ms
Power Consumption	75 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 0.3 m without plug
Number of products on MCB of 16 A type B 24	

GreenUp Lowbay G2

Temperature	
Ambient temperature range	-20 to +45 °C

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Gray
Optical cover finish	Frosted
Overall height	144 mm
Overall diameter	250 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Initial chromaticity	(0.313.0.324)SDCM<5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.01 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	40,000 hour(s)
Median useful life L90B50	20,000 hour(s)

Application Conditions	
Suitable for random switching	No

Product Data	
Order product name	BY288P LED90/CW PSU
Full product name	BY288P LED90/CW PSU
Full product code	872016972887500
Order code	911401508031
Material Nr. (12NC)	911401508031
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169728875
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169728875

Dimensional drawing

