



# GreenPerform Troffer

## RC100X LED37S 865 W60L60 IAO G3

GreenPerform Troffer, 116 lm/W, 865 cool daylight, InterAct office

GreenPerform troffer improves the compact design of the last generation with performance improvement and more variants for different markets. Integrating with all available system: POE, InterAct office wireless, InterAct Office Pro, ActiLume controller, GreenPerform troffer offers additional energy saving and connected features.

### Product data

<b>General Information</b>		<b>Optical cover type</b>	
Light source replaceable	No	Variable linear-lens array in polycarbonate cover	
Number of gear units	1 unit	<b>Operating and Electrical</b>	
Driver included	Yes	Input Voltage	220 to 240 V
Light source engine type	LED	Line Frequency	50 to 60 Hz
Glow-wire test	Temperature 600 °C, duration 30 s	Inrush current	21 A
Flammability mark	For mounting on normally flammable surfaces	Inrush time	280 ms
CE mark	CE mark	Power Consumption	32 W
Warranty period	3 years	Power Factor (Fraction)	0.9
<b>Light Technical</b>		Number of products on MCB of 16 A type B 21	
Luminous Flux	3,700 lm	<b>Temperature</b>	
Correlated Color Temperature (Nom)	6500 K	Ambient temperature range	-20 to +40 °C
Luminous Efficacy (rated) (Nom)	116 lm/W	<b>Controls and Dimming</b>	
Color rendering index (CRI)	80	Dimmable	Yes
Light source color	865 cool daylight	Control interface	InterAct office

## GreenPerform Troffer

Constant light output	No
-----------------------	----

### Mechanical and Housing

Housing Material	Metal
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Ribbed
Overall length	597 mm
Overall width	597 mm
Overall height	46 mm
Dimensions (Height x Width x Depth)	46 x 597 x 597 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Initial chromaticity	SDCM<4
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

### Application Conditions

Suitable for random switching	No
-------------------------------	----

### Product Data

Order product name	RC100X LED37S 865 W60L60 IAO G3
Full product name	RC100X LED37S 865 W60L60 IAO G3
Full product code	911401510651
Order code	911401510651
Material Nr. (12NC)	911401510651
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

## Dimensional drawing

