

# Greenperform Waterproof G2 - WT188C

## WT168C LED20 CW L1200 PSD

Greenperform Waterproof G2 – WT188C, 16 W, 2000 lm, 6500 K, DALI, 120°

Greenperform Waterproof G2 luminaire and its components are designed for both indoor and semi-outdoor application (anti-UV PC material housing and diffuser, stainless steel installation accessory). We design for friendly optical, energy saving, reliable quality, and easy wiring. Beyond that, GreenParking wireless motion detective system is ready to provide the maximum energy saving and new lighting experience to you.

### Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
Glow-wire test	Temperature 750 °C, duration 5 s
CE mark	CE mark
Warranty period	3 years
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	2,000 lm

Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	125 lm/W
Color rendering index (CRI)	>80
Light source color	865 cool daylight
Optic type	Symmetrical
Optical cover type	Polycarbonate bowl/cover foggy
Luminaire light beam spread	120°
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	22 A

Greenperform Waterproof G2 - WT188C

Inrush time	0.275 ms
Power Consumption	16 W
Power Factor (Fraction)	0.9
Connection	Screw connection block
Number of products on MCB of 16 A type B	38

Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	Gray and white
Optical cover finish	Opal
Overall length	1,183 mm
Overall width	84 mm
Overall height	83 mm
Dimensions (Height x Width x Depth)	83 x 84 x 1183 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	45,000 hour(s)
Median useful life L90B50	35,000 hour(s)


Application Conditions

Maximum dim level	1%
-------------------	----

Product Data

Order product name	WT168C LED20 CW L1200 PSD
Full product name	WT168C LED20 CW L1200 PSD
Full product code	911401512141
Order code	911401512141
Material Nr. (12NC)	911401512141
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing



## Greenperform Waterproof G2 - WT188C

