



SmartBright Troffer

RC098V LED22S/840 W60L60 CPC

SmartBright Troffer, 94 lm/W, 840 neutral white

SmartBright 2.0 troffer is the most affordable LED troffer delivering comfortable light with high quality. It offers two lumen options with three dimension types, 600x600, 300x1200 and 600x1200mm

Product data

General Information		Temperature	
Light source engine type	LED	Ambient temperature range	-20 to +40 °C
CE mark	CE mark		
Light Technical		Controls and Dimming	
Luminous Flux	2,450 lm	Dimmable	No
Correlated Color Temperature (Nom)	4000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	94 lm/W		
Color rendering index (CRI)	>80	Mechanical and Housing	
Light source color	840 neutral white	Housing Material	Steel
Optical cover type	Opal	Optical cover material	Polycarbonate
		Housing Color	White
Operating and Electrical		Optical cover finish	Opal
Input Voltage	220 to 240 V	Overall length	597 mm
Line Frequency	50 or 60 Hz	Overall width	597 mm
Power Consumption	26 W	Overall height	32 mm
Power Factor (Fraction)	0.9	Dimensions (Height x Width x Depth)	32 x 597 x 597 mm
Number of products on MCB of 16 A type B	24		
		Approval and Application	
		Ingress protection code	IP20 [Finger-protected]
		Mech. impact protection code	IK03 [0.3 J]

SmartBright Troffer

Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	RC098V LED22S/840 W60L60 CPC

Full product name	RC098V LED22S/840 W60L60 CPC
Full product code	911401515921
Order code	911401515921
Material Nr. (12NC)	911401515921
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing

