



# SmartBright Troffer

## RC098V LED22S/865 W30L120 PCV

SmartBright Troffer, 94 lm/W, 865 cool daylight

SmartBright 2.0 troffer is the most affordable LED troffer delivering comfortable light with high quality. It offers two lumen options with three dimension types, 600x600, 300x1200 and 600x1200mm

### Product data

Light Technical	
Luminous Flux	2,450 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	94 lm/W
Color rendering index (CRI)	>80
Light source color	865 cool daylight

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	26 W

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Overall length	1,197 mm

Overall width	297 mm
Overall height	32 mm
Dimensions (Height x Width x Depth)	32 x 297 x 1197 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Product Data	
Order product name	RC098V LED22S/865 W30L120 PCV
Full product name	RC098V LED22S/865 W30L120 PCV
Full product code	911401516521
Order code	911401516521
Material Nr. (12NC)	911401516521
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

## SmartBright Troffer

### Dimensional drawing

