



# SlimBalance

## RC551B LED20S 840 L60 PSU SD

SlimBalance, 111.11 lm/W, 840 neutral white

SlimBalance is a full range of product family with sleek and elegant design helps to create attractive and differentiated space for customers. The family covers different length (600mm, 1200mm, 1500mm), different end cap (round, square) and different light distribution (direct, indirect). Its office compliant version delivers comfortable light with good quality.

### Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

### Product data

General Information			
Light source replaceable	No	Correlated Color Temperature (Nom)	4000 K
Number of gear units	1 unit	Luminous Efficacy (rated) (Nom)	111.11 lm/W
Driver included	Yes	Color rendering index (CRI)	>80
Light source engine type	LED	Beam angle of light source	- degree(s)
Glow-wire test	Temperature 650 °C, duration 30 s	Light source color	840 neutral white
Flammability mark	-	Optic type	Wide beam
CE mark	CE mark	Optical cover type	Linear-lens array in polycarbonate cover
ENEC mark	-	Luminaire light beam spread	60°
Warranty period	3 years	Operating and Electrical	
EU RoHS compliant	Yes	Input Voltage	220/240 V
Light Technical		Line Frequency	50 to 60 Hz
Luminous Flux	2,000 lm	Inrush current	14 A
		Inrush time	250 ms

## SlimBalance

Power Consumption	18 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	-
Number of products on MCB of 16 A type B	33

### Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	-
Control interface	-
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum extruded
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Silver
Optical cover finish	Opal
Overall length	630 mm
Overall width	70 mm
Overall height	105 mm
Dimensions (Height x Width x Depth)	105 x 70 x 630 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM< 3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

### Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

### Product Data

Order product name	RC551B LED20S 840 L60 PSU SD
Full product name	RC551B LED20S 840 L60 PSU SD
Full product code	911401520241
Order code	911401520241
Material Nr. (12NC)	911401520241
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

### Dimensional drawing



