



GreenUp Highbay

BY550P LED200/CW PSU HRO

LED module 20600 lm, Cool white, Power supply unit (On/Off), High-rack optic

GreenUp Highbay BY550 is a high efficient and reliable LED highbay for industrial high-ceiling facilities without humid and dusty requirement, designed for both new project and retrofit. This lighting system can deliver up to 88% energy savings with the integrated G2 Actilume Wireless. It delivers point to point replace up to 400W HID and T5 6x54W higbay with easy installation. There are three beam shapes to choose with good light quality CRI85 and UGR 17. Integrated with G2 Actilume Wireless, GreenUp BY550 provide connected lighting with daylight , occupancy sensor, and ZigBee wireless communication, will increase your savings by upgrading to an intelligent system and delivering one-stop solution for your Factory, Warehouse, Distribution center, Indoor spot hall, and other high ceiling indoor application.

Product data

| General Information | |
|--------------------------|-----------------------------------|
| Lamp family code | LED206 [LED module 20600 lm] |
| Light source replaceable | No |
| Number of gear units | 2 units |
| Gear | - |
| Driver included | Yes |
| Glow-wire test | Temperature 650 °C, duration 30 s |
| Flammability mark | - |
| CE mark | CE mark |
| ENEC mark | - |

| Light Technical | |
|------------------------------------|--------------------------------|
| Correlated Color Temperature (Nom) | 6500 K |
| Color rendering index (CRI) | >85 |
| Light source color | Cool white |
| Optic type | High-rack optic |
| Optical cover type | Polycarbonate bowl/cover clear |
| Luminaire light beam spread | 100° |
| Operating and Electrical | |
| Input Voltage | 220-240 V |
| Line Frequency | 50 to 60 Hz |
| Power Consumption | 160 W |

GreenUp Highbay

| | |
|-------------------------|-------------------------------|
| Power Factor (Fraction) | 0.9 |
| Connection | Screw connection block 3-pole |
| Cable | - |

Temperature

| | |
|---------------------------|---------------|
| Ambient temperature range | -20 to +40 °C |
|---------------------------|---------------|

Controls and Dimming

| | |
|-------------------------------|----------------------------|
| Dimmable | No |
| Driver/power unit/transformer | Power supply unit (On/Off) |
| Constant light output | Yes |

Mechanical and Housing

| | |
|------------------|-------------------------|
| Housing Material | Metal-Plastic |
| Optic material | Polymethyl methacrylate |
| Housing Color | White |

Approval and Application

| | |
|------------------------------|-------------------------|
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK03 [0.3 J] |

| | |
|----------------------|----------------|
| Protection class IEC | Safety class I |
|----------------------|----------------|

Initial Performance (IEC Compliant)

| | |
|-----------------------------|---------|
| Luminous flux tolerance | +/-7.5% |
| Initial chromaticity | - |
| Power consumption tolerance | +/-10% |

Application Conditions

| | |
|-------------------|----------------|
| Maximum dim level | Not applicable |
|-------------------|----------------|

Product Data

| | |
|---------------------------------|--------------------------|
| Order product name | BY550P LED200/CW PSU HRO |
| Full product name | BY550P LED200/CW PSU HRO |
| Full product code | 911401521921 |
| Order code | 911401521921 |
| Material Nr. (12NC) | 911401521921 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |

Dimensional drawing

