



# GreenUp Highbay

## BY550P LED140/NW PSD WB

LED module 14000 lm, Neutral white, Power supply unit with DALI interface, Wide beam

GreenUp Highbay BY550 is a high efficient and reliable LED highbay for industrial high-ceiling facilities without humid and dusty requirement, designed for both new project and retrofit. This lighting system can deliver up to 88% energy savings with the integrated G2 Acticlume Wireless. It delivers point to point replace up to 400W HID and T5 6x54W higbay with easy installation. There are three beam shapes to choose with good light quality CRI85 and UGR 17. Integrated with G2 Acticlume Wireless, GreenUp BY550 provide connected lighting with daylight , occupancy sensor, and ZigBee wireless communication, will increase your savings by upgrading to an intelligent system and delivering one-stop solution for your Factory, Warehouse, Distribution center, Indoor spot hall, and other high ceiling indoor application.

### Product data

General Information	
Lamp family code	LED140 [LED module 14000 lm]
Light source replaceable	No
Number of gear units	2 units
Gear	-
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Flammability mark	-
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 30 s

Light Technical	
Luminous Flux	14,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color rendering index (CRI)	>85
Light source color	Neutral white
Optic type	Wide beam
Optical cover type	Polycarbonate bowl/cover clear
Luminaire light beam spread	90°

Operating and Electrical	
Input Voltage	220 to 240 V

# GreenUp Highbay

Line Frequency	50 to 60 Hz
Power Consumption	110 W
Power Factor (Fraction)	0.9
Connection	Screw connection block 3-pole
Cable	-
Number of products on MCB of 16 A type B	12

## Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	-
Constant light output	Yes

## Mechanical and Housing

Housing Material	Metal-Plastic
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Housing Color	White
Optical cover finish	Clear

## Approval and Application

Ingress protection code	IP20 [Finger-protected]
-------------------------	-------------------------

Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7.5%
Initial chromaticity	-
Power consumption tolerance	+/-10%

## Application Conditions

Maximum dim level	1% (depends on dimmer, ELV)
-------------------	-----------------------------

## Product Data

Order product name	BY550P LED140/NW PSD WB
Full product name	BY550P LED140/NW PSD WB
Full product code	911401523621
Order code	911401523621
Material Nr. (12NC)	911401523621
Local order code	BY550P110W4KDWB
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Dimensional drawing

