



SlimBalance

SP550P LED40S 840 L120 PSD SD CAU SQ

SlimBalance, 97.56 lm/W, 840 neutral white, DALI

SlimBalance is a full range of product family with sleek and elegant design helps to create attractive and differentiated space for customers. The family covers different length (600mm, 1200mm, 1500mm), different end cap (round, square) and different light distribution (direct, indirect). Its office compliant version delivers comfortable light with good quality.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data

General Information		Operating and Electrical	
Light source replaceable	No	Correlated Color Temperature (Nom)	4000 K
Number of gear units	1 unit	Luminous Efficacy (rated) (Nom)	97.56 lm/W
Driver included	Yes	Color rendering index (CRI)	>80
Light source engine type	LED	Beam angle of light source	- degree(s)
CE mark	CE mark	Light source color	840 neutral white
Warranty period	3 years	Optic type	Wide beam
Flammability mark	-	Optical cover type	Opal
ENEC mark	ENEC mark	Luminaire light beam spread	120°
Glow-wire test	Temperature 650 °C, duration 30 s		
EU RoHS compliant	Yes		
Light Technical			
Luminous Flux	4,000 lm	Input Voltage	220/240 V
		Line Frequency	50 to 60 Hz
		Inrush current	22 A
		Inrush time	275 ms

SlimBalance

Power Consumption	41 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	-
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Metal
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Silver
Optical cover finish	Opal
Overall length	1,230 mm
Overall width	70 mm
Overall height	105 mm
Dimensions (Height x Width x Depth)	105 x 70 x 1230 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM< 3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Application Conditions

Maximum dim level	1%
-------------------	----

Product Data

Order product name	SP550P LED40S 840 L120 PSD SD CAU SQ
Full product name	SP550P LED40S 840 L120 PSD SD CAU SQ
Full product code	911401531541
Order code	911401531541
Material Nr. (12NC)	911401531541
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing



