
PHILIPS Lighting



SlimBalance

SP551P LED20S 840 L60 PSU SD CAU

SlimBalance, 111.11 lm/W, 840 neutral white

SlimBalance is a full range of product family with sleek and elegant design helps to create attractive and differentiated space for customers. The family covers different length (600mm, 1200mm, 1500mm), different end cap (round, square) and different light distribution (direct, indirect). Its office compliant version delivers comfortable light with good quality.

Warnings and Safety

- The product is IPXO & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data


General Information		Correlated Color Temperature (Nom)	4000 K
Light source replaceable	No	Luminous Efficacy (rated) (Nom)	111.11 lm/W
Number of gear units	1 unit	Color rendering index (CRI)	>80
Driver included	Yes	Beam angle of light source	- degree(s)
Light source engine type	LED	Light source color	840 neutral white
Glow-wire test	Temperature 650 °C, duration 30 s	Optic type	Wide beam
Flammability mark	-	Optical cover type	Linear-lens array in polycarbonate cover
CE mark	CE mark	Luminaire light beam spread	60°
ENEC mark	ENEC mark		
Warranty period	3 years	Operating and Electrical	
EU RoHS compliant	Yes	Input Voltage	220/240 V
		Line Frequency	50 to 60 Hz
Light Technical		Inrush current	14 A
Luminous Flux	2,000 lm	Inrush time	250 ms

SlimBalance

Power Consumption	18 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	-
Number of products on MCB of 16 A type B	33
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	-
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Metal
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Silver
Optical cover finish	Opal
Overall length	630 mm
Overall width	70 mm
Overall height	105 mm
Dimensions (Height x Width x Depth)	105 x 70 x 630 mm

Approval and Application			
Ingress protection code	IP20 [Finger-protected]		
Mech. impact protection code	IK03 [0.3 J]		
Protection class IEC	Safety class I		
Initial Performance (IEC Compliant)			
Luminous flux tolerance	+/-10%		
Initial chromaticity	(0.38, 0.38) SDCM< 3		
Power consumption tolerance	+/-10%		
Over Time Performance (IEC Compliant)			
Median useful life L70B50	50,000 hour(s)		
Application Conditions			
Maximum dim level	Not applicable		
Product Data			
Order product name	SP551P LED20S 840 L60 PSU SD CAU		
Full product name	SP551P LED20S 840 L60 PSU SD CAU		
Full product code	911401532741		
Order code	911401532741		
Material Nr. (12NC)	911401532741		
Numerator - Quantity Per Pack	1		
Numerator - Packs per outer box	2		

Dimensional drawing





SlimBalance



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, October 30 - data subject to change