



SlimBalance

SP550P LED40S 840 L120 PSD CD CAU

SlimBalance, 97.56 lm/W, 840 neutral white, DALI

SlimBalance is a full range of product family with sleek and elegant design helps to create attractive and differentiated space for customers. The family covers different length (600mm, 1200mm, 1500mm), different end cap (round, square) and different light distribution (direct, indirect). Its office compliant version delivers comfortable light with good quality.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data

General Information		Correlated Color Temperature (Nom)	
Light source replaceable	No	Correlated Color Temperature (Nom)	4000 K
Number of gear units	1 unit	Luminous Efficacy (rated) (Nom)	97.56 lm/W
Driver included	Yes	Color rendering index (CRI)	>80
Light source engine type	LED	Beam angle of light source	- degree(s)
Glow-wire test	Temperature 650 °C, duration 30 s	Light source color	840 neutral white
Flammability mark	-	Optic type	Wide beam
CE mark	CE mark	Optical cover type	Opal
ENEC mark	-	Luminaire light beam spread	120°
Warranty period	3 years	Operating and Electrical	
EU RoHS compliant	Yes	Input Voltage	220/240 V
Light Technical		Line Frequency	50 to 60 Hz
Luminous Flux	4,000 lm	Inrush current	22 A
		Inrush time	275 ms

SlimBalance

Power Consumption	41 W
Power Factor (Fraction)	0.95
Connection	Internal connector
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	-
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Metal
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Silver
Optical cover finish	Opal
Overall length	1,200 mm
Overall width	70 mm
Overall height	105 mm
Dimensions (Height x Width x Depth)	105 x 70 x 1200 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM< 3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Application Conditions

Maximum dim level	1%
-------------------	----

Product Data

Order product name	SP550P LED40S 840 L120 PSD CD CAU
Full product name	SP550P LED40S 840 L120 PSD CD CAU
Full product code	911401534641
Order code	911401534641
Material Nr. (12NC)	911401534641
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing



