



GreenUp Highbay

BY550X LED100/CW ACW2 IS HRO

LED module 10500 lm, Cool white, High-rack optic

GreenUp Highbay BY550 is a high efficient and reliable LED highbay for industrial high-ceiling facilities without humid and dusty requirement, designed for both new project and retrofit. This lighting system can deliver up to 88% energy savings with the integrated G2 Actilume Wireless. It delivers point to point replace up to 400W HID and T5 6x54W highbay with easy installation. There are three beam shapes to choose with good light quality CRI85 and UGR 17. Integrated with G2 Actilume Wireless, GreenUp BY550 provide connected lighting with daylight , occupancy sensor, and ZigBee wireless communication, will increase your savings by upgrading to an intelligent system and delivering one-stop solution for your Factory, Warehouse, Distribution center, Indoor spot hall, and other high ceiling indoor application.

Product data

General Information	
Lamp family code	LED105 [LED module 10500 lm]
Light source replaceable	No
Number of gear units	1 unit
Gear	-
Driver included	Yes
CE mark	CE mark
Flammability mark	-
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Light Technical	
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	>85

Light source color	Cool white
Optic type	High-rack optic
Optical cover type	Polycarbonate bowl/cover clear
Luminaire light beam spread	90°
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Power Consumption	80 W
Power Factor (Fraction)	0.9
Connection	Screw connection block 3-pole
Cable	-

GreenUp Highbay

Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Constant light output	Yes

Mechanical and Housing

Housing Material	Metal–Plastic
Optic material	Polymethyl methacrylate
Housing Color	White

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7.5%
-------------------------	---------

Initial chromaticity	-
Power consumption tolerance	+/-10%

Application Conditions

Maximum dim level	1% (depends on dimmer, ELV)
-------------------	-----------------------------

Product Data

Order product name	BY550X LED100/CW ACW2 IS HRO
Full product name	BY550X LED100/CW ACW2 IS HRO
Full product code	911401538321
Order code	911401538321
Material Nr. (12NC)	911401538321
Local order code	BY550P80W6KWHR
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

