



Coreline tempo small

BVP110 LED42/NW A

Coreline tempo small, 4200 lm, 38 W, Neutral white, Asymmetrical, 39° x 96°, Safety class I, Mounting bracket adjustable

CoreLine tempo small is a highly-efficient range of luminaires designed for 1:1 retrofit replacement of conventional floodlighting technology, while retaining the same electrical installation and poles. This urban lighting range is designed for the direct replacement of 70W HID lamps, but uses less energy and requires less investment than conventional installations. A narrow range of options makes it easy to find the best lux-for-lux replacement for your project lighting.

Product data

General Information			
Lamp family code	LED42 [LED module 4200 lm]	CE mark	CE mark
Light source replaceable	No	Warranty period	5 years
Number of gear units	1 unit	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	ENEC mark	-
Remarks	* -Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test	Temperature 650 °C, duration 30 s
Light source engine type	LED	EU RoHS compliant	Yes
Service tag	Yes	Light Technical	
Lighting Technology	LED	Upward light output ratio	88
Value ladder	Performance	Luminous Flux	4,200 lm
		Standard tilt angle posttop	0°
		Standard tilt angle side entry	0°
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	111 lm/W
		Color rendering index (CRI)	80

Coreline tempo small

Number of light sources	40
Light source color	Neutral white
Optical cover type	Flat glass
Luminaire light beam spread	39° x 96°
Optic type outdoor	Asymmetrical

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	5 A
Inrush time	0.06 ms
Power Consumption	38 W
Power Factor (Fraction)	0.98
Connection	External connector
Cable	Cable 0.5 m with cable connector
Number of products on MCB of 16 A type B	95

Temperature

Ambient temperature range	-40 to +35 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Acrylate
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Aluminum and gray
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	285 mm
Overall width	254 mm
Overall height	52 mm

Effective projected area	0.052 m ²
Dimensions (Height x Width x Depth)	52 x 254 x 285 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.374, 0.369) SDCM <5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 75000 h	7.5 %
Lumen maintenance at median useful life* 75000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Order product name	BVP110 LED42/NW A
Full product name	BVP110 LED42/NW A
Full product code	871016330635300
Order code	911401555231
Material Nr. (12NC)	911401555231
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163306353
Numerator - Packs per outer box	1
EAN/UPC - Case	8710163306353

Coreline tempo small

Dimensional drawing

