



GreenUp Wellglass

BY200P LED40 L-B/CW PSU

LED module, system flux 3800 lm, Cool white, Power supply unit (On/Off)

GreenUp LED Wellglass luminaire is designed to replace traditional WelGlass up to 70W with only 35% of the load for similar illumination. It is a perfect LED solution for outdoor application and industry of harsh condition like power plant, metal, and non hazardous area in chemical and petrochemical industry. Compared to conventional HID WelGlass, it improves reliability, comfort, while reducing energy and maintenance cost dramatically. GreenUp Wellglass comes with 2 different mounting, pipe and bracket, and comes with 2 beam, lambertian and batwing.

Product data

General Information		Color rendering index (CRI)	
Lamp family code	LED38S [LED module, system flux 3800 lm]	Light source color	>80
Light source replaceable	No	Optic type	Cool white
Number of gear units	1 unit	Optical cover type	Wide beam
Gear	-	Luminaire light beam spread	Polycarbonate bowl/cover frosted
Driver included	Yes		120°
Light source engine type	LED	Operating and Electrical	
CE mark	-	Input Voltage	220 to 240 V
Flammability mark	-	Line Frequency	50 to 60 Hz
ENEC mark	-	Power Consumption	38 W
Glow-wire test	Temperature 650 °C, duration 30 s	Power Factor (Fraction)	0.95
		Connection	-
Light Technical		Number of products on MCB of 16 A type B 24	
Luminous Flux	3,600 lm		
Correlated Color Temperature (Nom)	6500 K		
Luminous Efficacy (rated) (Nom)	90 lm/W		

GreenUp Wellglass

Temperature	
Ambient temperature range	-30 to +40 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	Yes
Mechanical and Housing	
Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Dark gray
Optical cover finish	Opal
Overall height	255 mm
Overall diameter	215 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7.5%
Initial chromaticity	-
Power consumption tolerance	+/-10%
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	BY200P LED40 L-B/CW PSU
Full product name	BY200P LED40 L-B/CW PSU
Full product code	911401563721
Order code	911401563721
Material Nr. (12NC)	911401563721
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

