



GreenSpace Downlight G4

DN292B 1xDLED-3000 PSU WH

GreenSpace Downlight G4, 16 W, 1500 lm, 3000 K, Beam angle 60 to 120°, Matte, Finger-protected

GreenSpace Gen4 is the new LED downlight with high efficacy (95~ 100lm/W) delivering substantial energy saving. It offers diverse configurations within 600~2,000lm. GreenSpace Gen4 could apply to shopping mall, retail store and office application with different variants . The lifetime is 50,000 hours (L70 @ 25C)

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Light source engine type	LED
CE mark	CE mark
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Light Technical	
Luminous Flux	1,500 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	85 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Light source color	830 warm white
Optic type	Beam angle 60 to 120°
Optical cover type	Transparent bowl with white cover

Luminaire light beam spread	90°
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	16 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	15
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-

GreenSpace Downlight G4

Constant light output	Yes
-----------------------	-----

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	White
Optical cover finish	Matte

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

Over Time Performance (IEC Compliant)




Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Product Data

Order product name	DN292B 1xDLED-3000 PSU WH
Full product name	DN292B 1xDLED-3000 PSU WH
Full product code	911401566121
Order code	911401566121
Material Nr. (12NC)	911401566121
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12

Dimensional drawing

Dimension 灯具尺寸	A (mm)	B (mm)
DN290B 1xDLED / ALU	95 / 99	Φ 122
DN291B 1xDLED / ALU	105 / 109	Φ 167
DN292B 1xDLED / ALU	114 / 118	Φ 218
DN293B 1xDLED / ALU	114 / 118	Φ 218



Dimension 灯具尺寸	A (mm)	B (mm)
DN290B 1xDLED / ALU	95 / 99	Φ 122
DN291B 1xDLED / ALU	105 / 109	Φ 167
DN292B 1xDLED / ALU	114 / 118	Φ 218
DN293B 1xDLED / ALU	114 / 118	Φ 218

