



GreenSpace Downlight G4

DN290B 1xDLED-4000 PSU WH CAU

GreenSpace Downlight G4, 6.5 W, 4000 K, Beam angle 60 to 120°, Finger-protected

GreenSpace Gen4 is the new LED downlight with high efficacy (95~ 100lm/W) delivering substantial energy saving. It offers diverse configurations within 600~2,000lm. GreenSpace Gen4 could apply to shopping mall, retail store and office application with different variants . The lifetime is 50,000 hours (L70 @ 25C)

Product data

General Information		Power Consumption	
Light source replaceable	No	6.5 W	
Number of gear units	1 unit	Power Factor (Fraction)	
CE mark	CE mark	0.9	
ENEC mark	-	Cable	
Glow-wire test	Temperature 650 °C, duration 30 s	Cord with plug SAA 3-pole	
Light Technical		Temperature	
Correlated Color Temperature (Nom)	4000 K	Ambient temperature range	
Number of light sources	1	-20 to +40 °C	
Light source color	840 neutral white	Controls and Dimming	
Optic type	Beam angle 60 to 120°	Dimmable	
Optical cover type	Transparent bowl with white cover	No	
Luminaire light beam spread	90°	Driver/power unit/transformer	
Operating and Electrical		Power supply unit (On/Off)	
Input Voltage	220-240 V	Constant light output	
		Yes	
		Mechanical and Housing	
		Housing Material	
		Aluminum	
		Reflector material	
		Polycarbonate	
		Optic material	
		Polycarbonate	

GreenSpace Downlight G4

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	DN290B 1xDLED-4000 PSU WH CAU

Full product name	DN290B 1xDLED-4000 PSU WH CAU
Full product code	871016330042999
Order code	911401568521
Material Nr. (12NC)	911401568521
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163300429
Numerator - Packs per outer box	36

Dimensional drawing

Dimension 灯具尺寸	A (mm)	B (mm)
DN290B 1xDLED / ALU	95 / 99	Φ 122
DN291B 1xDLED / ALU	105 / 109	Φ 167
DN292B 1xDLED / ALU	114 / 118	Φ 218
DN293B 1xDLED / ALU	114 / 118	Φ 218

