



GreenSpace G5

DN392B LED16/830 POE D150 WH GC

GreenSpace G5, 14.5 W, 1500 lm, 3000 K, Power over Ethernet, High-gloss high reflectance, Matte, Finger-protected

GreenSpace Gen5 is a new LED downlight range combining light efficiency and comfort with product diversity and system compatibility

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
CE mark	-
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light Technical	
Luminous Flux	1,500 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	103 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	85 degree(s)
Light source color	830 warm white
Optic type	High-gloss high reflectance
Optical cover type	Transparent bowl with white cover

Luminaire light beam spread	80°
Operating and Electrical	
Input Voltage	53 V
Line Frequency	- Hz
Power Consumption	14.5 W
Power Factor (Fraction)	1
Number of products on MCB of 16 A type B	-
Temperature	
Ambient temperature range	0 to +40 °C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Luminaire controller with power over Ethernet
Control interface	Power over Ethernet
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast

GreenSpace G5

Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Black and white
Optical cover finish	Matte
Overall length	0 mm
Overall width	0 mm
Overall height	100 mm
Overall diameter	162 mm
Dimensions (Height x Width x Depth)	100 x 0 x 0 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class III

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.44,0.403) SDCM<5

Power consumption tolerance	+/-10%
-----------------------------	--------

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.16 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	43,000 hour(s)
Median useful life L90B50	20,000 hour(s)

Product Data

Order product name	DN392B LED16/830 POE D150 WH GC
Full product name	DN392B LED16/830 POE D150 WH GC
Full product code	911401575741
Order code	911401575741
Material Nr. (12NC)	911401575741
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

