



# GreenPerform Highbay LED

## BY618P LED200/CW PSU HRO

LED module 20000 lm, Cool white, Power supply unit (On/Off), High-rack optic

Customers in industrial and warehousing applications are constantly looking for ways to reduce the amount of energy required to light their facilities. The GreenPerform LED Highbay luminaire can directly replace 250 and 400 W HID high-bays, thereby generating significant energy savings. When there is a power failure, downtime is reduced with GreenPerform LED Highbay, as it turns on instantly, compared to the slow run-up of HID lamps. The luminaire comes with high-quality optics, ensuring excellent lighting performance in different application areas. The high-rack optics are specially designed to illuminate vertical planes in warehouses. With a choice of mounting methods, installation is easy and secure.

### Product data

General Information	
Lamp family code	LED200 [LED module 20000 lm]
Flammability mark	For mounting on normally flammable surfaces
Light Technical	
Luminous Flux	21,000 lm
Luminous Efficacy (rated) (Nom)	100 lm/W
Light source color	Cool white
Optic type	High-rack optic
Operating and Electrical	
Input Voltage	220 to 240 V

Line Frequency	50 to 60 Hz
Power Consumption	210 W
Controls and Dimming	
Driver/power unit/transformer	Power supply unit (On/Off)
Mechanical and Housing	
Housing Color	RAL standard (to be defined)
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

GreenPerform Highbay LED

Protection class IEC	Safety class I
Product Data	
Order product name	BY618P LED200/CW PSU HRO
Full product name	BY618P LED200/CW PSU HRO
Full product code	911401577701
Order code	911401577701

Material Nr. (12NC)	911401577701
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291995845
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291995845

Dimensional drawing

