



GreenPerform Highbay LED

BY618P LED200/NW PSU WB

LED module 20000 lm, Neutral white, Power supply unit (On/Off), Wide beam

Customers in industrial and warehousing applications are constantly looking for ways to reduce the amount of energy required to light their facilities. The GreenPerform LED Highbay luminaire can directly replace 250 and 400 W HID high-bays, thereby generating significant energy savings. When there is a power failure, downtime is reduced with GreenPerform LED Highbay, as it turns on instantly, compared to the slow run-up of HID lamps. The luminaire comes with high-quality optics, ensuring excellent lighting performance in different application areas. The high-rack optics are specially designed to illuminate vertical planes in warehouses. With a choice of mounting methods, installation is easy and secure.

Product data

| | | | |
|---------------------------------|---|--|--|
| General Information | | Line Frequency | |
| Lamp family code | LED200 [LED module 20000 lm] | 50 to 60 Hz | |
| Flammability mark | For mounting on normally flammable surfaces | Power Consumption | |
| | | 210 W | |
| Light Technical | | Controls and Dimming | |
| Luminous Flux | 21,000 lm | Driver/power unit/transformer | |
| Luminous Efficacy (rated) (Nom) | 100 lm/W | Power supply unit (On/Off) | |
| Light source color | Neutral white | Mechanical and Housing | |
| Optic type | Wide beam | Housing Color | |
| | | RAL standard (to be defined) | |
| Operating and Electrical | | Approval and Application | |
| Input Voltage | 220 to 240 V | Ingress protection code | |
| | | IP65 [Dust penetration-protected, jet-proof] | |

GreenPerform Highbay LED

| | |
|----------------------|-------------------------|
| Protection class IEC | Safety class I |
| Product Data | |
| Order product name | BY618P LED200/NW PSU WB |
| Full product name | BY618P LED200/NW PSU WB |
| Full product code | 911401577801 |

| | |
|---------------------------------|--------------|
| Order code | 911401577801 |
| Material Nr. (12NC) | 911401577801 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |

Dimensional drawing

