



# GreenPerform Highbay LED

## BY618P LED200/CW PSU NB

LED module 20000 lm, Cool white, Power supply unit (On/Off), Narrow beam

Customers in industrial and warehousing applications are constantly looking for ways to reduce the amount of energy required to light their facilities. The GreenPerform LED Highbay luminaire can directly replace 250 and 400 W HID high-bays, thereby generating significant energy savings. When there is a power failure, downtime is reduced with GreenPerform LED Highbay, as it turns on instantly, compared to the slow run-up of HID lamps. The luminaire comes with high-quality optics, ensuring excellent lighting performance in different application areas. The high-rack optics are specially designed to illuminate vertical planes in warehouses. With a choice of mounting methods, installation is easy and secure.

### Product data

<b>General Information</b>		<b>Line Frequency</b>	
Lamp family code	LED200 [LED module 20000 lm]	50 to 60 Hz	
Flammability mark	For mounting on normally flammable surfaces	<b>Power Consumption</b>	
		210 W	
<b>Light Technical</b>		<b>Controls and Dimming</b>	
Luminous Flux	21,000 lm	Driver/power unit/transformer	
Luminous Efficacy (rated) (Nom)	100 lm/W	Power supply unit (On/Off)	
Light source color	Cool white	<b>Mechanical and Housing</b>	
Optic type	Narrow beam	Housing Color	
		RAL standard (to be defined)	
<b>Operating and Electrical</b>		<b>Approval and Application</b>	
Input Voltage	220 to 240 V	Ingress protection code	
		IP65 [Dust penetration-protected, jet-proof]	

GreenPerform Highbay LED

Protection class IEC	Safety class I
Product Data	
Order product name	BY618P LED200/CW PSU NB
Full product name	BY618P LED200/CW PSU NB
Full product code	911401578001

Order code	911401578001
Material Nr. (12NC)	911401578001
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

