



GreenPerform Highbay LED

BY619P LED100/CW PSU NB

LED module 10000 lm, Cool white, Power supply unit (On/Off),
Narrow beam

Customers in industrial and warehousing applications are constantly looking for ways to reduce the amount of energy required to light their facilities. The GreenPerform LED Highbay luminaire can directly replace 250 and 400 W HID high-bays, thereby generating significant energy savings. When there is a power failure, downtime is reduced with GreenPerform LED Highbay, as it turns on instantly, compared to the slow run-up of HID lamps. The luminaire comes with high-quality optics, ensuring excellent lighting performance in different application areas. The high-rack optics are specially designed to illuminate vertical planes in warehouses. With a choice of mounting methods, installation is easy and secure.

Product data

General Information		Line Frequency		50 to 60 Hz
Lamp family code	LED100 [LED module 10000 lm]	Power Consumption		110 W
Flammability mark	For mounting on normally flammable surfaces	Controls and Dimming		
Light Technical		Driver/power unit/transformer		Power supply unit (On/Off)
Luminous Flux	11,000 lm	Mechanical and Housing		
Luminous Efficacy (rated) (Nom)	100 lm/W	Housing Color		RAL standard (to be defined)
Light source color	Cool white	Approval and Application		
Optic type	Narrow beam	Ingress protection code		IP65 [Dust penetration-protected, jet-proof]
Operating and Electrical				
Input Voltage	220 to 240 V			

GreenPerform Highbay LED

Protection class IEC	Safety class I
Product Data	
Order product name	BY619P LED100/CW PSU NB
Full product name	BY619P LED100/CW PSU NB
Full product code	911401578201

Order code	911401578201
Material Nr. (12NC)	911401578201
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

