



GreenSpace Downlight G4

DN292B 1xDLED-3000 PSU WH CAU

GreenSpace Downlight G4, 16 W, Beam angle 60 to 120°, Finger-protected

GreenSpace Gen4 is the new LED downlight with high efficacy (95~ 100lm/W) delivering substantial energy saving. It offers diverse configurations within 600~2,000lm. GreenSpace Gen4 could apply to shopping mall, retail store and office application with different variants . The lifetime is 50,000 hours (L70 @ 25C)

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
CE mark	CE mark
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 30 s

Light Technical	
Number of light sources	1
Light source color	830 warm white
Optic type	Beam angle 60 to 120°
Optical cover type	Transparent bowl with white cover
Luminaire light beam spread	90°

Operating and Electrical	
Input Voltage	220-240 V
Power Consumption	16 W

Power Factor (Fraction)	0.9
Cable	Cord with plug SAA 3-pole

Temperature	
Ambient temperature range	-20 to +40 °C

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	Yes

Mechanical and Housing	
Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Polycarbonate

GreenSpace Downlight G4

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%



Product Data

Order product name	DN292B 1xDLED-3000 PSU WH CAU
--------------------	-------------------------------

Full product name	DN292B 1xDLED-3000 PSU WH CAU
Full product code	871016330057399
Order code	911401581021
Material Nr. (12NC)	911401581021
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163300573
Numerator - Packs per outer box	12

Dimensional drawing

Dimension 灯具尺寸	A (mm)	B (mm)
DN290B 1xDLED / ALU	95 / 99	Φ 122
DN291B 1xDLED / ALU	105 / 109	Φ 167
DN292B 1xDLED / ALU	114 / 118	Φ 218
DN293B 1xDLED / ALU	114 / 118	Φ 218



Dimension 灯具尺寸	A (mm)	B (mm)
DN290B 1xDLED / ALU	95 / 99	Φ 122
DN291B 1xDLED / ALU	105 / 109	Φ 167
DN292B 1xDLED / ALU	114 / 118	Φ 218
DN293B 1xDLED / ALU	114 / 118	Φ 218

