



# Essential SmartBright LED Downlight

## DN004B LED12/WW D150 RD

Essential SmartBright G2 LED Downlight is value for money product with high efficacy, good quality and reliability. It offers multiple configurations from 300lm to 2000lm output, to replace conventional downlight. It can be used for shopping mall, retail store, residential and office. It's an ideal product family to distribute in trade market.

### Product data

General Information		Temperature	
Light source replaceable	No	Ambient temperature range	-20 to +40 °C
Lighting Technology	LED		
Warranty period	1 years	Controls and Dimming	
		Dimmable	No
		Driver/power unit/transformer	Power supply unit (On/Off)
Light Technical		Mechanical and Housing	
Luminous Flux	1,200 lm	Housing Material	Plastic
Correlated Color Temperature (Nom)	3000 K	Reflector material	Polycarbonate
Color rendering index (CRI)	80	Optic material	Polycarbonate
Light source color	3000/4000/6500	Housing Color	White
Luminaire light beam spread	110°	Overall length	33 mm
		Overall width	33 mm
		Overall height	33 mm
		Overall diameter	175 mm
		Dimensions (Height x Width x Depth)	33 x 33 x 33 mm
Operating and Electrical		Approval and Application	
Line Frequency	50 or 60 Hz	Ingress protection code	IP20 [Finger-protected]
Input Frequency	50 or 60 Hz		
Power Consumption	15 W		
Power Factor (Fraction)	0.7		
Connection	Flying leads/wires		

## Essential SmartBright LED Downlight

Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
<b>Initial Performance (IEC Compliant)</b>	
Initial chromaticity	SDCM<5
Power consumption tolerance	+/-10%
<b>Product Data</b>	
Order product name	DN004B LED12/WW D150 RD
Full product name	DN004B LED12/WW D150 RD

Full product code	692382862431699
Order code	911401599131
Material Nr. (12NC)	911401599131
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828624316
Numerator - Packs per outer box	24
EAN/UPC - Case	6923828624163

### Dimensional drawing

