



Tango G2 LED

BVP283 LED280/NW 280W 220-240V AWBE

Tango G2 LED, 28000 lm, 280 W, 740 neutral white, Asymmetrical wide beam, 16° x 80°, Safety class I, Mounting bracket adjustable

Tango G2 LED is a general purpose LED flood lighting luminaire for various lighting applications, such as area lighting, bill-board, façade, industry area, recreational sports and other general applications. The Tango G2 LED flood light incorporates LED light source, optical system, heat sink and driver into one compact housing. Its specially designed heat sink incorporates aesthetics and functionality to ensure reliability and long lifetime. Tango G2 LED takes advantage of LED technology which provides energy savings and a longer lifetime, bringing area lighting into a new era.

Product data

General Information		Luminaire light beam spread	
Light source replaceable	Yes	Luminaire light beam spread	16° x 80°
Driver included	Yes	Optic type outdoor	Asymmetrical wide beam
Light source engine type	LED	Operating and Electrical	
Lighting Technology	LED	Input Voltage	220-240 V
CE mark	CE mark	Line Frequency	50 or 60 Hz
Warranty period	3 years	Power Consumption	280 W
		Power Factor (Fraction)	0.95
		Connection	Flying leads/wires
		Cable	Cable 1.5 m without plug
Light Technical		Temperature	
Luminous Flux	28,000 lm	Ambient temperature range	-40 to +45 °C
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	100 lm/W		
Color rendering index (CRI)	>70		
Light source color	740 neutral white		
Optical cover type	Glass		

Tango G2 LED

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Optic material	Polymethyl methacrylate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Aluminum and gray
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Overall length	480 mm
Overall width	655 mm
Overall height	60 mm
Effective projected area	0.25 m ²
Dimensions (Height x Width x Depth)	60 x 655 x 480 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
-------------------------	--

Mech. impact protection code	IK07 [2 J reinforced]
Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<=7
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP283 LED280/NW 280W 220-240V AWBE
Full product name	BVP283 LED280/NW 280W 220-240V AWBE
Full product code	911401605603
Order code	911401605603
Material Nr. (12NC)	911401605603
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

