



Tango G2 LED

BVP283 LED210/NW 210W 220-240V AWBE

Tango G2 LED, 21000 lm, 210 W, 740 neutral white, Asymmetrical wide beam, 16° x 80°, Safety class I, Mounting bracket adjustable

Tango G2 LED is a general purpose LED flood lighting luminaire for various lighting applications, such as area lighting, bill-board, façade, industry area, recreational sports and other general applications. The Tango G2 LED flood light incorporates LED light source, optical system, heat sink and driver into one compact housing. Its specially designed heat sink incorporates aesthetics and functionality to ensure reliability and long lifetime. Tango G2 LED takes advantage of LED technology which provides energy savings and a longer lifetime, bringing area lighting into a new era.

Product data

General Information		Luminaire light beam spread	
Light source replaceable	Yes	16° x 80°	
Driver included	Yes	Optic type outdoor	
Light source engine type	LED	Asymmetrical wide beam	
Lighting Technology	LED		
CE mark	CE mark		
Warranty period	3 years		
Light Technical		Operating and Electrical	
Luminous Flux	21,000 lm	Input Voltage	220-240 V
Correlated Color Temperature (Nom)	4000 K	Line Frequency	50 or 60 Hz
Luminous Efficacy (rated) (Nom)	100 lm/W	Power Consumption	210 W
Color rendering index (CRI)	>70	Power Factor (Fraction)	0.95
Light source color	740 neutral white	Connection	Flying leads/wires
Optical cover type	Glass	Cable	Cable 1.5 m without plug
		Temperature	
		Ambient temperature range	-40 to +45 °C

Tango G2 LED

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum die cast
Optic material	Polymethyl methacrylate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Aluminum and gray
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Overall length	480 mm
Overall width	655 mm
Overall height	60 mm
Effective projected area	0.25 m²
Dimensions (Height x Width x Depth)	60 x 655 x 480 mm

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Mech. impact protection code	IK07 [2 J reinforced]
Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<=7
Power consumption tolerance	+/-10%

Product Data	
Order product name	BVP283 LED210/NW 210W 220-240V AWBE
Full product name	BVP283 LED210/NW 210W 220-240V AWBE
Full product code	911401605803
Order code	911401605803
Material Nr. (12NC)	911401605803
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

