



UNIdot

BGS302 42xLED-HB-4000 24V D140

UNIdot, 506 lm, 6.8 W, Neutral white, Safety class III

The right façade lighting enhances the ambiance of any space and sparks imagination. Philips UNIdot is just one of the latest innovations in LED ighting that lets you create that perfect atmosphere both for the outdoor and the indoor. Dreamy starry nights, and captivating urban landscapes are all made possible with the smart Philips UNIdot LED lighting system. Flexible and modular, UNIdot lights can be affixed on any challenging façade, fulfilling the most creative lighting design brief. Available in dimmable color options, with light intensity that is easy to adjust, this makes a great replacement for conventional solutions in terms of performance, versatility, light quality and energy savings.

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	No
Light source engine type	LED
Lighting Technology	LED
CE mark	CE mark
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	-
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	506 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	-

Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	74 lm/W
Color rendering index (CRI)	70
Light source color	Neutral white
Optical cover type	Polycarbonate bowl/cover frosted
Operating and Electrical	
Input Voltage	24 DC V
Power Consumption	6.8 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires
Cable	Cable 0.3 m without plug
Temperature	
Ambient temperature range	-20 to +50 °C

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Electronic transformer
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	Gray and white
Mounting device	-
Optical cover shape	Hemispherical flat
Optical cover finish	Frosted
Overall height	51 mm
Overall diameter	140 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
-------------------------	--

Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class III

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

Product Data

Order product name	BGS302 42xLED-HB-4000 24V D140
Full product name	BGS302 42xLED-HB-4000 24V D140
Full product code	911401612703
Order code	911401612703
Material Nr. (12NC)	911401612703
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	27

Dimensional drawing