



CitySpirit Street LED

BDS480 LED70/WW PSU 220-240V DW2 MP1

CitySpirit Street LED, 7000 lm, 75 W, Warm white, Distribution street pedestrian, Safety class I, Post-top for diameter 60 mm

Vibrant outdoor lighting has the power to revitalise a city's spirit, transforming it into an exciting, uplifting space where residents and visitors feel safe and at home even after dark. Philips CitySpirit Street LED is luminaire designed to provide quality, environmentally friendly lighting that seamlessly integrates into the urban landscape. Equipped with LED technology and consistent light output, this luminaire delivers efficient and excellent lighting to any city.

Product data


General Information			
Lamp family code	-	Correlated Color Temperature (Nom)	3000 K
Light source replaceable	Yes	Luminous Efficacy (rated) (Nom)	93.33 lm/W
Number of gear units	-	Color rendering index (CRI)	70
Driver included	Yes	Light source color	Warm white
Light source engine type	LED	Optical cover type	Acrylate micro-lens optic clear
CE mark	-	Luminaire light beam spread	-
Warranty period	3 years	Optic type outdoor	Distribution street pedestrian
Flammability mark	-	Operating and Electrical	
ENEC mark	-	Input Voltage	200 to 240 V
EU RoHS compliant	No	Line Frequency	50 to 60 Hz
Light Technical		Inrush current	46 A
Upward light output ratio	0	Inrush time	440 ms
Luminous Flux	7,000 lm	Power Consumption	75 W
Standard tilt angle posttop	-	Power Factor (Fraction)	0.95
Standard tilt angle side entry	-	Connection	Flying leads/wires
		Cable	Cable 6.0 m without plug

CitySpirit Street LED

Number of products on MCB of 16 A type B -	
Temperature	
Ambient temperature range	-40 to +35 °C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	Glass
Optic material	Glass
Optical cover material	Polymethyl methacrylate
Fixation material	Stainless steel
Housing Color	Dark gray
Mounting device	Post-top for diameter 60 mm
Optical cover shape	Convex lens
Optical cover finish	Clear
Overall length	640 mm
Overall width	150 mm
Overall height	454 mm
Overall diameter	60 mm
Dimensions (Height x Width x Depth)	454 x 150 x 640 mm

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	4/2 kV
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM>5
Power consumption tolerance	+/-10%
Application Conditions	
Maximum dim level	0% (digital)
Product Data	
Order product name	BDS480 LED70/WW PSU 220-240V DW2 MP1
Full product name	BDS480 LED70/WW PSU 220-240V DW2 MP1
Full product code	911401617803
Order code	01617803
Material Nr. (12NC)	911401617803
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing



CitySpirit Street LED

