



Tango G2 LED

BVP282 LED176/NW 160W 220-240V SWB

Tango G2 LED, Safety class I

Tango G2 LED is a general purpose LED flood lighting luminaire for various lighting applications, such as area lighting, bill-board, façade, industry area, recreational sports and other general applications. The Tango G2 LED flood light incorporates LED light source, optical system, heat sink and driver into one compact housing. Its specially designed heat sink incorporates aesthetics and functionality to ensure reliability and long lifetime. Tango G2 LED takes advantage of LED technology which provides energy savings and a longer lifetime, bringing area lighting into a new era.

Product data

| | | | |
|---------------------------------|-------------------|---------------------------------|--|
| General Information | | Optical cover material | |
| Driver included | Yes | Polycarbonate | |
| Lighting Technology | LED | Approval and Application | |
| CE mark | CE mark | Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
| Light Technical | | Mech. impact protection code | IK07 [2 J reinforced] |
| Color rendering index (CRI) | 80 | Protection class IEC | Safety class I |
| Operating and Electrical | | Product Data | |
| Input Voltage | 220-240 V | Order product name | BVP282 LED176/NW 160W 220-240V SWB |
| Line Frequency | 50 to 60 Hz | Full product name | BVP282 LED176/NW 160W 220-240V SWB |
| Temperature | | Full product code | 911401666302 |
| Ambient temperature range | -40 to +50 °C | Order code | 911401666302 |
| Mechanical and Housing | | Material Nr. (12NC) | 911401666302 |
| Housing Material | Aluminum extruded | Numerator - Quantity Per Pack | 1 |
| Optic material | Polycarbonate | Numerator - Packs per outer box | 1 |

Tango G2 LED

Dimensional drawing

