



# Flex Cove G4

## LS161S LED8 824 IP44 L5000

Flex Cove G4, 800 lm, 75 lm/W, Amber, 24 V, Wire-protected, splash-proof

Sustainable and flexible offering with excellent optical performance

### Product data

| General Information      |   |
|--------------------------|---|
| Light source replaceable | No  |
| Number of gear units     | 1 unit                                      |
| Driver included          | No  |
| Light source engine type | LED   |
| CE mark                  | CE mark                                     |
| Warranty period          | 3 years                                     |
| Flammability mark        | For mounting on normally flammable surfaces |
| Glow-wire test           | Temperature 650 °C, duration 5 s            |
| EU RoHS compliant        | Yes   |

| Light Technical                    |               |
|------------------------------------|---------------|
| Luminous Flux                      | 800 lm        |
| Correlated Color Temperature (Nom) | 2400 K        |
| Luminous Efficacy (rated) (Nom)    | 75 lm/W       |
| Color rendering index (CRI)        | >80           |
| Beam angle of light source         | 120 degree(s) |
| Light source color                 | Amber         |
| Optical cover type                 | -             |
| Luminaire light beam spread        | 120° x 120°   |

| Operating and Electrical                 |         |
|--|---------|
| Input Voltage                            | 24 V    |
| Line Frequency                           | - Hz    |
| Inrush current                           | 35 A    |
| Inrush time                              | 0.32 ms |
| Power Consumption                        | 8.4 W   |
| Power Factor (Fraction)                  | 0       |
| Number of products on MCB of 16 A type B | -       |

| Temperature               |               |
|---------------------------|---------------|
| Ambient temperature range | -20 to +35 °C |

| Controls and Dimming  |              |
|-----------------------|--------------|
| Dimmable              | Yes          |
| Control interface     | Dynamix DMX  |
| Constant light output | Programmable |

| Mechanical and Housing |          |
|------------------------|----------|
| Optical cover material | -        |
| Housing Color          | White    |
| Optical cover finish   | -        |
| Overall length         | 5,000 mm |

Flex Cove G4

|                                     |                  |
|-------------------------------------|------------------|
| Overall width                       | 11 mm            |
| Overall height                      | 6 mm             |
| Overall diameter                    | 0 mm             |
| Dimensions (Height x Width x Depth) | 6 x 11 x 5000 mm |

Approval and Application

|                              |                                     |
|------------------------------|-------------------------------------|
| Ingress protection code      | IP44 [Wire-protected, splash-proof] |
| Mech. impact protection code | IK02 [0.2 J standard]               |
| Protection class IEC         | -                                   |

Initial Performance (IEC Compliant)

|                             |        |
|-----------------------------|--------|
| Luminous flux tolerance     | +/-10% |
| Initial chromaticity        | 3      |
| Power consumption tolerance | +/-10% |

Over Time Performance (IEC Compliant)

|                           |                |
|---------------------------|----------------|
| Median useful life L70B50 | 30,000 hour(s) |
|---------------------------|----------------|

Application Conditions

|                               |    |
|-------------------------------|----|
| Maximum dim level             | 1% |
| Suitable for random switching | No |

Product Data

|                                 |                            |
|---------------------------------|----------------------------|
| Order product name              | LS161S LED8 824 IP44 L5000 |
| Full product name               | LS161S LED8 824 IP44 L5000 |
| Full product code               | 911401690803               |
| Order code                      | 911401690803               |
| Material Nr. (12NC)             | 911401690803               |
| Numerator - Quantity Per Pack   | 1                          |
| Numerator - Packs per outer box | 10                         |

Dimensional drawing

