



# Essential SmartBright LED Downlight

## DN003B LED3/CW L100 SQ

Essential SmartBright G2 LED Downlight is value for money product with high efficacy, good quality and reliability. It offers multiple configurations from 300lm to 2000lm output, to replace conventional downlight. It can be used for shopping mall, retail store, residential and office. It's an ideal product family to distribute in trade market.

### Product data

General Information	
Light source replaceable	No
Lighting Technology	LED
Warranty period	1 years
Light Technical	
Luminous Flux	300 lm
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	80
Light source color	3000/4000/6500
Luminaire light beam spread	110°
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	4 W
Power Factor (Fraction)	0.7
Connection	Flying leads/wires

Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Mechanical and Housing	
Housing Material	Plastic
Reflector material	Polycarbonate
Optic material	Polycarbonate
Housing Color	White
Overall length	125 mm
Overall width	125 mm
Overall height	33 mm
Overall diameter	225 mm
Dimensions (Height x Width x Depth)	33 x 125 x 125 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

## Essential SmartBright LED Downlight

Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II
<b>Initial Performance (IEC Compliant)</b>	
Initial chromaticity	SDCM<5
Power consumption tolerance	+/-10%
<b>Product Data</b>	
Order product name	DN003B LED3/CW L100 SQ
Full product name	DN003B LED3/CW L100 SQ

Full product code	692382862572699
Order code	911401711342
Material Nr. (12NC)	911401711342
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828625726
Numerator - Packs per outer box	24
EAN/UPC - Case	6923828625849

### Dimensional drawing

