



# LuxSpace CN

## DN498 1xDLED-4000 PSU-E C WH PG CAU

LuxSpace CN, 20 W, 2000 lm, 4000 K, Matt mirror, Finger-protected; dust accumulation-protected, splash-proof

LuxSpace Gen3 is the new LED downlight with extremely high efficacy(up to 100lm/W) delivering substantial energy saving. It adopts a brand-new LED platform and optical technology for visual comfort. It has the wide portfolio with multiple lumen and dimension options and is designed with DALI and IP54 (only front side) versions for various applications

### Warnings and Safety

- 1.The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
- 2.For indoor use at room temperature
- 3.When cleaning the product, please use dry soft cotton cloth only
- 4.Don't switch on before complete installation
- 5.If the power cord gets damaged within the warranty period, please have it replaced by Philips nominated dealer
- 6.The luminaire shall, under no circumstances be covered or abutted with building insulation or be installed in a residential installation
- 7.Do not hot swap! LED heat sink module must not be disconnected with line power on failure. To do so may damage the product
- 8.Luminaire must not be used or stored in corrosive environment where hazardous material such as Sulphur, Chlorine, Phthalates, etc, are present

### Product data

General Information		Flammability mark	
Light source replaceable	No	ENEC mark	-
Number of gear units	1 unit	Glow-wire test	Temperature 750 °C, duration 5 s
Driver included	Yes	EU RoHS compliant	No
CE mark	-		
Warranty period	3 years		

Light Technical	
Luminous Flux	2,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	- degree(s)
Light source color	840 neutral white
Optic type	Matt mirror
Luminaire light beam spread	60°

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	20 A
Inrush time	0.15 ms
Power Consumption	20 W
Power Factor (Fraction)	0.9
Connection	-
Cable	Cable with plug
Number of products on MCB of 16 A type B	50

Temperature	
Ambient temperature range	-20 to +40 °C

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	Aluminum
Optic material	Polycarbonate
Optical cover material	-
Fixation material	-

Housing Color	Black and white
Optical cover finish	-
Overall height	124 mm
Overall diameter	218 mm

Approval and Application	
Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7.5%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	1.00 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	40,000 hour(s)
Median useful life L90B50	20,000 hour(s)

Application Conditions	
Suitable for random switching	No

Product Data	
Order product name	DN498 1xDLED-4000 PSU-E C WH PG CAU
Full product name	DN498 1xDLED-4000 PSU-E C WH PG CAU
Full product code	911401803799
Order code	911401803799
Material Nr. (12NC)	911401803799
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing



