



# FlowBase

## BWP352 LED274/NW 240W 220-240V DM2 MP1

FlowBase, 25700 lm, 240 W, 740 neutral white, Safety class I

A lighting design that ensures safety and good visibility is a key element in the success of any tunnel project. Philips FlowBase combines compact design, reliability, and affordability in one complete package to bring the perfect lighting solution for any tunnel application.

### Product data

<b>General Information</b>		<b>Controls and Dimming</b>	
Driver included	Yes	Dimmable	No
CE mark	CE mark	Driver/power unit/transformer	Power supply unit (On/Off)
ENEC mark	-	Constant light output	No
<b>Light Technical</b>		<b>Mechanical and Housing</b>	
Luminous Flux	25,700 lm	Housing Material	Aluminum
Correlated Color Temperature (Nom)	4000 K	Optic material	Polycarbonate
Luminous Efficacy (rated) (Nom)	107.1 lm/W	Fixation material	Aluminum
Light source color	740 neutral white	<b>Approval and Application</b>	
<b>Operating and Electrical</b>		Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Input Voltage	220-240 V	Mech. impact protection code	IK08 [5 J vandal-protected]
Line Frequency	50 to 60 Hz	Protection class IEC	Safety class I
Power Consumption	240 W	<b>Over Time Performance (IEC Compliant)</b>	
Power Factor (Fraction)	0.95	Median useful life L70B50	50,000 hour(s)
<b>Temperature</b>			
Ambient temperature range	-40 to +50 °C		

## Application Conditions

Maximum dim level	10%
-------------------	-----

## Product Data

Order product name	BWP352 LED274/NW 240W 220-240V DM2 MP1
Full product name	BWP352 LED274/NW 240W 220-240V DM2 MP1
Full product code	911401809198

Order code	911401809198
------------	--------------

Material Nr. (12NC)	911401809198
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	1
---------------------------------	---

## Dimensional drawing

