



# GreenUp Waterproof

## WT118C LED45 NW PSD L1500 ENG

GreenUp Waterproof, 46 W, 4800 lm, 4000 K, DALI, 120°

GreenUp Waterproof is a high efficient and reliable LED luminaire, designed for industrial application with humid and dust protection requirement. It delivers significant energy savings of up to 62% as compared to conventional dual-T8 waterproof. Utilization of UV-shield PC and extrusion process makes it suitable for semi-outdoor environments, and together with the built-in breather ensure a sound performance. With professional optic design and Philips LED module gives the most comfortable light experience of CRI 85.

### Product data

General Information			
Lamp family code	LED48S [LED module, system flux 4800 lm]	Beam angle of light source	120 degree(s)
Light source replaceable	No	Light source color	Neutral white
Number of gear units	1 unit	Optic type	Symmetrical
Gear	-	Optical cover type	Opal
Driver included	Yes	Luminaire light beam spread	120°
Glow-wire test	Temperature 650 °C, duration 5 s	Operating and Electrical	
Flammability mark	-	Input Voltage	220-240 V
CE mark	CE mark	Line Frequency	50 to 60 Hz
ENEC mark	-	Inrush current	22 A
Warranty period	3 years	Inrush time	275 ms
EU RoHS compliant	Yes	Power Consumption	46 W
Light Technical		Power Factor (Fraction)	0.9
Luminous Flux	4,800 lm	Connection	Flying leads/wires
Correlated Color Temperature (Nom)	4000 K	Cable	Cable 0.3 m without plug
Luminous Efficacy (rated) (Nom)	104.35 lm/W	Number of products on MCB of 16 A type B 24	
Color rendering index (CRI)	>80		

GreenUp Waterproof

Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	DALI
Constant light output	No
Mechanical and Housing	
Housing Material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	Gray and white
Optical cover finish	Opal
Overall length	1,450 mm
Overall width	50 mm
Overall height	70 mm
Dimensions (Height x Width x Depth)	70 x 50 x 1450 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class I

Dimensional drawing

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<5
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	1 %
Median useful life L70B50	40,000 hour(s)
Median useful life L80B50	38,000 hour(s)
Median useful life L90B50	35,000 hour(s)
Application Conditions	
Maximum dim level	1%
Product Data	
Order product name	WT118C LED45 NW PSD L1500 ENG
Full product name	WT118C LED45 NW PSD L1500 ENG
Full product code	911401821699
Order code	911401821699
Material Nr. (12NC)	911401821699
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4

