

Smartbright Waterproof G2

WT066C NW LED9 L600 PSU TW

Smartbright Waterproof G2, 9.4 W, 900 lm, 4000 K, 120°

SmartBright Waterproof G2 is an innovation from SmartBright Waterproof G1, can be used to replace traditional waterproof luminaires with fluorescent lamps or LED tubes, provides quality of light with substantial energy & maintenance savings. The luminaire and its components are designed for both indoor and semi-outdoor application (anti-UV PC material housing and diffuser), it is an ideal lighting solution for canopy, food industry, parking garages, car washers. Beyond that, SmartBright Waterproof G2 is also maintenance free by seal for life integral design, and reliable 25K hrs lifetime.

Product data

General Information		Light Technical	
Light source replaceable	No	Luminous Flux	900 lm
Number of gear units	1 unit	Correlated Color Temperature (Nom)	4000 K
Driver included	Yes	Luminous Efficacy (rated) (Nom)	90 lm/W
Light source engine type	LED	Color rendering index (CRI)	>80
Service tag	Yes	Beam angle of light source	- degree(s)
Glow-wire test	Temperature 750 °C, duration 5 s	Light source color	Neutral white
Flammability mark	-	Optic type	Symmetrical
CE mark	CE mark	Optical cover type	Polycarbonate bowl/cover opal
ENEC mark	-	Luminaire light beam spread	120°
Warranty period	3 years	Operating and Electrical	
EU RoHS compliant	Yes	Input Voltage	220 to 240 V
		Line Frequency	50 to 60 Hz

Smartbright Waterproof G2

Inrush current	5.1 A
Inrush time	0.1 ms
Power Consumption	9.4 W
Power Factor (Fraction)	0.9
Connection	Screw connection block
Cable	-
Number of products on MCB of 16 A type B	100

Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	Gray and white
Optical cover finish	Opal
Overall length	654 mm
Overall width	68 mm
Overall height	60 mm
Dimensions (Height x Width x Depth)	60 x 68 x 654 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
-------------------------	--

Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.0022 %
Median useful life L70B50	25,000 hour(s)
Median useful life L80B50	17,500 hour(s)
Median useful life L90B50	8,100 hour(s)


Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

Product Data

Order product name	WT066C NW LED9 L600 PSU TW
Full product name	WT066C NW LED9 L600 PSU TW
Full product code	871016331178499
Order code	911401823697
Material Nr. (12NC)	911401823697
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163311784
Numerator - Packs per outer box	4
EAN/UPC - Case	8710163312088

Dimensional drawing



Smartbright Waterproof G2

