



Essential Smartbright LED

BVP161 LED90/NW 100W 220-240V WB GOLD GM

Essential Smartbright LED, 9000 lm, 100 W, 740 neutral white, Symmetrical, 30° x 80°, Safety class I, Mounting bracket adjustable

Philips Essential SmartBright LED Floodlight not only ensures savings on initial capital, but also delivers reliable operational savings.

Product data

General Information			
Lamp family code	LED90 [LED module 9000 lm]	Standard tilt angle posttop	-
Light source replaceable	No	Standard tilt angle side entry	-
Number of gear units	1 unit	Correlated Color Temperature (Nom)	4000 K
Driver included	Yes	Luminous Efficacy (rated) (Nom)	90.00 lm/W
Light source engine type	LED	Color rendering index (CRI)	>70
Lighting Technology	LED	Light source color	740 neutral white
CE mark	CE mark	Optical cover type	Micro-lens optic in polycarbonate cover, wide
Warranty period	3 years	Luminaire light beam spread	30° x 80°
Flammability mark	-	Optic type outdoor	Symmetrical
ENEC mark	-		
EU RoHS compliant	No		
Light Technical		Operating and Electrical	
Upward light output ratio	0	Input Voltage	220 to 240 V
Luminous Flux	9,000 lm	Line Frequency	50 to 60 Hz
		Inrush current	0.64 A
		Inrush time	1.2 ms

Essential Smartbright LED

Power Consumption	100 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires
Cable	Cable 0.6 m without plug
Number of products on MCB of 16 A type B	22

Temperature

Ambient temperature range	-40 to +45 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Gold
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Optical cover finish	Frosted
Overall length	315.5 mm
Overall width	233.5 mm
Overall height	41 mm
Effective projected area	0.075 m²
Dimensions (Height x Width x Depth)	41 x 234 x 316 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Surge Protection (Common/Differential)	EN61547 (L-L 2kV, L-G 4kV) kV
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM<5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	1.00 %
-------------------------------	--------


Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

Product Data

Order product name	BVP161 LED90/NW 100W 220-240V WB GOLD GM
Full product name	BVP161 LED90/NW 100W 220-240V WB GOLD GM
Full product code	911401823698
Order code	911401823698
Material Nr. (12NC)	911401823698
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6

Dimensional drawing



Essential Smartbright LED

