



# SportsStar- BVP621/BVP622/ EVP622

## BVP621 LED672/NW 640W 220-240V AWB GM

SportsStar-BVP621/BVP622/EVP622, 67200 lm, 640 W, Neutral white, Asymmetrical wide beam, 15° x 95°, Safety class I, Mounting bracket adjustable

Philips SportsStar LED Floodlight sets the standard in high quality optical distribution with high performance and low light pollution (or effective light control). From Sports to Area Lighting, our system, including the high masts needed, projects the light exactly where it should be going. Choose the right illumination levels for any given setting with Philips SportsStar LED Floodlight.

### Product data

General Information		EU RoHS compliant	
Lamp family code	-	No	
Light source replaceable	Yes		
Number of gear units	1 unit		
Driver included	Yes		
Light source engine type	LED		
Lighting Technology	LED		
Flammability mark	-		
CE mark	CE mark		
ENEC mark	-		
Warranty period	3 years		
Light Technical			
Luminous Flux	67,200 lm		
Standard tilt angle posttop	-		
Standard tilt angle side entry	-		
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	105.00 lm/W		
Color rendering index (CRI)	70		
Light source color	Neutral white		
Optical cover type	Polycarbonate micro lens optic		
Luminaire light beam spread	15° x 95°		

Optic type outdoor	Asymmetrical wide beam
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	640 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 1.5 m without plug
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum extruded
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White and black
Mounting device	Mounting bracket adjustable
Optical cover shape	-
Optical cover finish	Frosted
Overall length	680 mm

Overall width	610 mm
Overall height	307 mm
Effective projected area	0.42 m²
Dimensions (Height x Width x Depth)	307 x 610 x 680 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<7
Power consumption tolerance	+/-10%
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	BVP621 LED672/NW 640W 220-240V AWB GM
Full product name	BVP621 LED672/NW 640W 220-240V AWB GM
Full product code	911401825098
Order code	911401825098
Material Nr. (12NC)	911401825098
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing



