



# SportsStar- BVP621/BVP622/ EVP622

## BVP621 LED912/WW 960W 220-240V SMB GM

SportsStar-BVP621/BVP622/EVP622, 91200 lm, 960 W, Warm white, Symmetrical medium beam, 50°, Safety class I, Mounting bracket adjustable

Philips SportsStar LED Floodlight sets the standard in high quality optical distribution with high performance and low light pollution (or effective light control). From Sports to Area Lighting, our system, including the high masts needed, projects the light exactly where it should be going. Choose the right illumination levels for any given setting with Philips SportsStar LED Floodlight.

### Product data

General Information		EU RoHS compliant	
Lamp family code	-		No
Light source replaceable	Yes	Light Technical	
Number of gear units	2 units	Luminous Flux	91,200 lm
Driver included	Yes	Standard tilt angle posttop	-
Light source engine type	LED	Standard tilt angle side entry	-
Lighting Technology	LED	Correlated Color Temperature (Nom)	3000 K
Flammability mark	-	Luminous Efficacy (rated) (Nom)	95.00 lm/W
CE mark	CE mark	Color rendering index (CRI)	70
ENEC mark	-	Light source color	Warm white
Warranty period	3 years	Optical cover type	Polycarbonate micro lens optic
		Luminaire light beam spread	50°

# SportsStar-BVP621/BVP622/EVP622

Optic type outdoor	Symmetrical medium beam
--------------------	-------------------------

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	960 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 1.5 m without plug

## Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

## Mechanical and Housing

Housing Material	Aluminum extruded
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White and black
Mounting device	Mounting bracket adjustable
Optical cover shape	-
Optical cover finish	Frosted
Overall length	680 mm
Overall width	740 mm

Overall height	307 mm
Effective projected area	0.42 m <sup>2</sup>
Dimensions (Height x Width x Depth)	307 x 740 x 680 mm

## Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
Protection class IEC	Safety class I

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<7
Power consumption tolerance	+/-10%

## Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

## Product Data

Order product name	BVP621 LED912/WW 960W 220-240V SMB
	GM
Full product name	BVP621 LED912/WW 960W 220-240V SMB
	GM
Full product code	911401825198
Order code	911401825198
Material Nr. (12NC)	911401825198
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Dimensional drawing



