



## Smartbright Waterproof G2

Inrush current	12.5 A
Inrush time	0.1 ms
Power Consumption	40 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires
Cable	Cable 0.3 m without plug
Number of products on MCB of 16 A type B	45

### Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

### Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	Gray and white
Optical cover finish	Opal
Overall length	1,226 mm
Overall width	68 mm
Overall height	60 mm
Dimensions (Height x Width x Depth)	60 x 68 x 1226 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
-------------------------	--

Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<5
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.0022 %
Median useful life L70B50	25,000 hour(s)
Median useful life L80B50	17,500 hour(s)
Median useful life L90B50	8,100 hour(s)


### Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

### Product Data

Order product name	WT066C NW LED36 L1200 PSU FW
Full product name	WT066C NW LED36 L1200 PSU FW
Full product code	871016331194499
Order code	911401825297
Material Nr. (12NC)	911401825297
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163311944
Numerator - Packs per outer box	4
EAN/UPC - Case	8710163312248

## Dimensional drawing



## Smartbright Waterproof G2

