



# SportsStar- BVP621/BVP622/ EVP622

## BVP621 LED504/CW 480W 220-240V NB GM

SportsStar-BVP621/BVP622/EVP622, 50400 lm, 480 W, Cool white, Narrow beam, 13°, Safety class I, Mounting bracket adjustable

Philips SportsStar LED Floodlight sets the standard in high quality optical distribution with high performance and low light pollution (or effective light control). From Sports to Area Lighting, our system, including the high masts needed, projects the light exactly where it should be going. Choose the right illumination levels for any given setting with Philips SportsStar LED Floodlight.

### Product data

General Information		EU RoHS compliant	
Lamp family code	-	No	
Light source replaceable	Yes	Light Technical	
Number of gear units	1 unit	Luminous Flux	50,400 lm
Driver included	Yes	Standard tilt angle posttop	-
Light source engine type	LED	Standard tilt angle side entry	-
Lighting Technology	LED	Correlated Color Temperature (Nom)	5700 K
Flammability mark	-	Luminous Efficacy (rated) (Nom)	105.00 lm/W
CE mark	CE mark	Color rendering index (CRI)	70
ENEC mark	-	Light source color	Cool white
Warranty period	3 years	Optical cover type	Polycarbonate micro lens optic
		Luminaire light beam spread	13°

SportsStar-BVP621/BVP622/EVP622

Optic type outdoor	Narrow beam
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	480 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 1.5 m without plug
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum extruded
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White and black
Mounting device	Mounting bracket adjustable
Optical cover shape	-
Optical cover finish	Frosted
Overall length	680 mm

Dimensional drawing

Overall width	520 mm
Overall height	307 mm
Effective projected area	0.42 m²
Dimensions (Height x Width x Depth)	307 x 520 x 680 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<7
Power consumption tolerance	+/-10%
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	BVP621 LED504/CW 480W 220-240V NB GM
Full product name	BVP621 LED504/CW 480W 220-240V NB GM
Full product code	911401826598
Order code	911401826598
Material Nr. (12NC)	911401826598
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

