



Xtend LED

RC115B LED35S/840 PSU W30L120 S

Xtend LED, 840 neutral white

Xtend LED is the new generation of linear design troffer with good illuminating uniformity and high efficiency

Product data

General Information	
Lamp family code	LED22 [LED module 2200 lm]
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
CE mark	CE mark
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Light Technical	
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	80
Number of light sources	1
Light source color	840 neutral white
Optic type	Beam angle 60 to 120°
Optical cover type	Transparent bowl with white cover
Luminaire light beam spread	110° x 110°
Operating and Electrical	
Input Voltage	220-240 V
Power Consumption	36.5 W

Power Factor (Fraction)	0.9
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	Yes
Mechanical and Housing	
Housing Material	Steel
Reflector material	Steel
Optic material	Polymethyl methacrylate
Housing Color	White
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Xtend LED

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	RC115B LED35S/840 PSU W30L120 S
Full product name	RC115B LED35S/840 PSU W30L120 S

Full product code	911401830799
Order code	01830799
Material Nr. (12NC)	911401830799
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing

