



SmartBright Panel

RC099V LED26S/840 W60L60 SUS GM

SmartBright Panel, 840 neutral white

SmartBright Panel is the most affordable LED panel delivering comfortable light with excellent uniformity

Product data


General Information		Controls and Dimming	
Light source replaceable	No	Dimmable	No
Number of gear units	1 unit	Driver/power unit/transformer	Power supply unit (On/Off)
Driver included	Yes	Constant light output	Yes
Glow-wire test	Temperature 650 °C, duration 30 s	Mechanical and Housing	
CE mark	CE mark	Housing Material	Steel
ENEC mark	-	Reflector material	Steel
Light Technical		Optic material	Polycarbonate
Correlated Color Temperature (Nom)	4000 K	Housing Color	White
Color rendering index (CRI)	80	Approval and Application	
Number of light sources	12	Ingress protection code	IP20 [Finger-protected]
Light source color	840 neutral white	Mech. impact protection code	IK02 [0.2 J standard]
Optic type	Beam angle 60 to 120°	Protection class IEC	Safety class I
Optical cover type	Transparent bowl with white cover	Initial Performance (IEC Compliant)	
Luminaire light beam spread	110° x 110°	Luminous flux tolerance	+/-10%
Operating and Electrical		Power consumption tolerance	+/-10%
Input Voltage	220-240 V	Product Data	
Power Factor (Fraction)	0.9	Order product name	RC099V LED26S/840 W60L60 SUS GM

Full product name	RC099V LED26S/840 W60L60 SUS GM
Full product code	911401834399
Order code	911401834399
Material Nr. (12NC)	911401834399


Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing

Product Type	Size LxWxH(mm)
RC099V LED26S W60x60 GH	597x297x25
RC099V LED26S W60x120 GH	1197x297x25
RC099V LED26S W60x60 SUS GH	603x603x75
RC099V LED26S W60x120 SUS GH	1203x603x75
RC099V LED26S W60x60 PCV GH	603x603x75
RC099V LED26S W60x120 PCV GH	1203x603x75
RC099V LED26S W60x60 GH	597x297x25
RC099V LED26S W60x120 GH	1197x297x25
RC099V LED26S W60x60 SUS GH	603x603x75
RC099V LED26S W60x120 SUS GH	1203x603x75
RC099V LED26S W60x60 PCV GH	603x603x75
RC099V LED26S W60x120 PCV GH	1203x603x75




RC099V LED26S W60x60 GH
RC099V LED26S W60x120 SUS GH
RC099V LED26S W60x60 PCV GH
RC099V LED26S W60x120 SUS GH




RC099V LED26S W60x120 GH
RC099V LED26S W60x120 SUS GH
RC099V LED26S W60x120 PCV GH
RC099V LED26S W60x120 SUS GH

Product Type	Size LxWxH(mm)
RC099V LED26S W60x60 GH	597x297x25
RC099V LED26S W60x120 GH	1197x297x25
RC099V LED26S W60x60 SUS GH	603x603x75
RC099V LED26S W60x120 SUS GH	1203x603x75
RC099V LED26S W60x60 PCV GH	603x603x75
RC099V LED26S W60x120 PCV GH	1203x603x75
RC099V LED26S W60x60 GH	597x297x25
RC099V LED26S W60x120 GH	1197x297x25
RC099V LED26S W60x60 SUS GH	603x603x75
RC099V LED26S W60x120 SUS GH	1203x603x75
RC099V LED26S W60x60 PCV GH	603x603x75
RC099V LED26S W60x120 PCV GH	1203x603x75



RC099V LED26S W60x60 GH
RC099V LED26S W60x120 SUS GH
RC099V LED26S W60x60 PCV GH
RC099V LED26S W60x120 SUS GH



RC099V LED26S W60x120 GH
RC099V LED26S W60x120 SUS GH
RC099V LED26S W60x120 PCV GH
RC099V LED26S W60x120 SUS GH

