



SmartBright Panel

RC099V LED26S/840 W30L120 SUS GM

SmartBright Panel, 840 neutral white

SmartBright Panel is the most affordable LED panel delivering comfortable light with excellent uniformity

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Glow-wire test	Temperature 650 °C, duration 30 s
CE mark	CE mark
ENEC mark	-
Light Technical	
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	80
Number of light sources	12
Light source color	840 neutral white
Optic type	Beam angle 60 to 120°
Optical cover type	Transparent bowl with white cover
Luminaire light beam spread	110° x 110°
Operating and Electrical	
Input Voltage	220-240 V
Power Factor (Fraction)	0.9


Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	Yes
Mechanical and Housing	
Housing Material	Steel
Reflector material	Steel
Optic material	Polycarbonate
Housing Color	White
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	RC099V LED26S/840 W30L120 SUS GM

Full product name	RC099V LED26S/840 W30L120 SUS GM
Full product code	911401834599
Order code	911401834599
Material Nr. (12NC)	911401834599


Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing

Product Type	Size LxWxH(mm)
RC099V LED26S WxHxLxS GM	397x297x75
RC099V LED26S WxHxLxS GM	1197x297x75
RC099V LED26S WxHxLxS GM	402x402x75
RC099V LED26S WxHxLxS SUS GM	1203x303x75
RC099V LED26S WxHxLxS PCV GM	402x402x75
RC099V LED26S WxHxLxS SUS GM	1203x303x75
RC099V LED26S WxHxLxS GM	397x297x75
RC099V LED26S WxHxLxS GM	1197x297x75
RC099V LED26S WxHxLxS SUS GM	402x402x75
RC099V LED26S WxHxLxS SUS GM	1203x303x75
RC099V LED26S WxHxLxS GM	397x297x75
RC099V LED26S WxHxLxS GM	1197x297x75
RC099V LED26S WxHxLxS SUS GM	402x402x75
RC099V LED26S WxHxLxS SUS GM	1203x303x75
RC099V LED26S WxHxLxS GM	397x297x75
RC099V LED26S WxHxLxS GM	1197x297x75
RC099V LED26S WxHxLxS SUS GM	402x402x75
RC099V LED26S WxHxLxS SUS GM	1203x303x75




RC099V LED26S WxHxLxS GM
RC099V LED26S WxHxLxS SUS GM
RC099V LED26S WxHxLxS PCV GM
RC099V LED26S WxHxLxS SUS GM
RC099V LED26S WxHxLxS PCV GM




RC099V LED26S WxHxLxS GM
RC099V LED26S WxHxLxS SUS GM
RC099V LED26S WxHxLxS PCV GM
RC099V LED26S WxHxLxS SUS GM
RC099V LED26S WxHxLxS PCV GM

Product Type	Size LxWxH(mm)
RC099V LED26S WxHxLxS GM	397x297x75
RC099V LED26S WxHxLxS GM	1197x297x75
RC099V LED26S WxHxLxS SUS GM	402x402x75
RC099V LED26S WxHxLxS SUS GM	1203x303x75
RC099V LED26S WxHxLxS PCV GM	402x402x75
RC099V LED26S WxHxLxS SUS GM	1203x303x75
RC099V LED26S WxHxLxS GM	397x297x75
RC099V LED26S WxHxLxS GM	1197x297x75
RC099V LED26S WxHxLxS SUS GM	402x402x75
RC099V LED26S WxHxLxS SUS GM	1203x303x75
RC099V LED26S WxHxLxS GM	397x297x75
RC099V LED26S WxHxLxS GM	1197x297x75
RC099V LED26S WxHxLxS SUS GM	402x402x75
RC099V LED26S WxHxLxS SUS GM	1203x303x75
RC099V LED26S WxHxLxS GM	397x297x75
RC099V LED26S WxHxLxS GM	1197x297x75
RC099V LED26S WxHxLxS SUS GM	402x402x75
RC099V LED26S WxHxLxS SUS GM	1203x303x75



RC099V LED26S WxHxLxS GM
RC099V LED26S WxHxLxS SUS GM
RC099V LED26S WxHxLxS PCV GM
RC099V LED26S WxHxLxS SUS GM
RC099V LED26S WxHxLxS PCV GM



RC099V LED26S WxHxLxS GM
RC099V LED26S WxHxLxS SUS GM
RC099V LED26S WxHxLxS PCV GM
RC099V LED26S WxHxLxS SUS GM
RC099V LED26S WxHxLxS PCV GM

